


Термостат KSD9700



Code	Action temperature (°C)	Reset temperature	Voltage AC(V)	Current (A)
55	55±5	≥30±10	250	5
60	60±5	40±10	250	5
65	65±5	45±10	250	5
70	70±5	50±10	250	5
75	75±5	55±10	250	5
80	80±5	55±10	250	5
85	85±5	60±10	250	5
90	90±5	65±10	250	5
95	95±5	70±10	250	5
100	100±5	75±10	250	5

Code	Action temperature (°C)	Reset temperature	Voltage AC(V)	Current (A)
105	105±5	80±10	250	5
110	110±5	80±10	250	5
115	115±5	85±10	250	5
120	120±5	90±10	250	5
125	125±5	95±10	250	5
130	130±5	100±15	250	5
135	135±5	105±15	250	5
140	140±5	110±15	250	5
145	145±5	115±15	250	5
150	150±5	120±15	250	5